

PAUL-GOTHE-GmbH Bochum

Wittener Straße 82
D-44789 Bochum



Manual for carrying box for the washing bottle

In the delivery capacity:

PVC-box, aluminum plate, 3 counter sink screws
(M8 x 16 mm), 3 wing nuts (M 6 mm)

Mounting at suction tube:

For the mounting at the suction must use the flange (Art.-No.: 45.04). This flange is in the delivery capacity of the big heater (Art.-No: 35.06) and can unscrewed from the heater. The flange will be fixed with the three counter sink screws (M8 x 16 mm) at the carrying box for the washing bottle.

To adapt the high of the bubbler use the wing nuts.

The suction tube will be fixed with the three Allen screws (M 8 x 25 mm).

Mounting with heater at suction tube:

The flange will be fixed at the heater with the three hexagonal screws (M8 x 20 mm) and the carrying box with the three counter sink screws. The suction tube will be fixed with the three Allen screws.

